

Part No: 163B-040CLSR

Valves

Y-Check Valve

Desc: 4 PVC CLR T/U Y-CHECK VALVE SRFPT FKM

MSRP: 1636.88

Part Code: 628

Weight(lbs): 21.065

Weight(kg): 9.555

Weight(gm): 9555

Size: 4"


Color: CLEAR

Material: PVC

Connection SR Fipt (True Union)

Body Color Clear

O-Ring FKM



A = 13- 5/8

A1 = 16- 3/4

B = 19- 9/32

C = 22- 5/16

D = 9-25/32

E = 6-17/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

