

Part No: 172B-010C

Valves

Y-Pattern Valve

Desc: 1 CPVC T/U Y-PATTERN VALVE FPT EPDM

MSRP: 239.33

Part Code: 622

Weight(lbs): 1.515

Weight(kg): 0.687

Weight(gm): 687

Size: 1"


Color: GRAY

Material: CPVC

Connection Fipt (True Union)

Body Color Gray

O-Ring EPDM



A = 6-5/8

A1 = 9-1/8

B = 7-3/8

C = 9

D = 5-3/8

E = 2-5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

