

Part No: 172B-020CSR

Valves

Y-Pattern Valve

Desc: 2 CPVC T/U Y-PATTERN VALVE SRFPT EPDM

MSRP: 806.26

Part Code: 622

Weight(lbs): 5.487

Weight(kg): 2.489

Weight(gm): 2489

Size: 2"


Color: GRAY

Material: CPVC

Connection SR Fipt (True Union)

Body Color Gray

O-Ring EPDM



A = 10-11/16

A1 = 14- 9/16

B = 10-13/16

C = 12-13/16

D = 8- 5/8

E = 3- 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

