

Part No: 173B-030C

Valves

Y-Pattern Valve

Desc: 3 CPVC T/U Y-PATTERN VALVE FPT FKM

MSRP: 1289.57

Part Code: 622

Weight(lbs): 13.823

Weight(kg): 6.27

Weight(gm): 6270

Size: 3"


Color: GRAY

Material: CPVC

Connection Fipt (True Union)

Body Color Gray

O-Ring FKM



A = 15-5/8

A1 = 21-1/8

B = 15-3/8

C = 18-3/16

D = 12-1/2

E = 6-5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

