

Part No: 1821V-015CSR

All

BV-1

Desc: 1-1/2 CPVC TU2K IND BV SR/THD EPDM VENTD

MSRP: 342.87

Part Code: 602

Weight(lbs): 1.664

Weight(kg): 0.755

Weight(gm): 755

Size: 1-1/2

Color:

Material:

Connection SR Threaded Ends EPDM

Under

Development

A = 3- 9/16

B = 3-23/32

C = 5-17/32

D = 4

E = 4- 3/16

Cv = 357

Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

