

Part No: 18236-060C

All

BV-1

Desc: 6 CPVC TU2K IND BV FLG EPDM W/TEE HANDLE

MSRP: 6120.07

Part Code: 613

Weight(lbs): 50.567

Weight(kg): 22.937

Weight(gm): 22937

Size: 6

Color:

Material:

Connection Flanged EPDM

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

