

Part No: 183901M-040C

All

BV-1

Desc: 40MM CPVC TEE VALVE SOC/THD FKM

MSRP: 371.99

Part Code: 264

Weight(lbs): 1.872

Weight(kg): 0.849

Weight(gm): 849

Size:

Color:

Material:

Connection FKM, Socket

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

