

Part No: 1882-060C

Nipples

Nipple

Desc: 1/2X6 CPVC NIPPLE TOE SCH80

MSRP: 10.18

Part Code: 121

Weight(lbs): 0.112

Weight(kg): 0.051

Weight(gm): 51

Size: 1/2" x 6"

Color: GRAY

Material: CPVC

Nipple Type TOE (Plain x Mipt)



L = 6

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

