

**Part No:** 1884-220C

**Nipples**

**Nipple**

**Desc:** 1X22 CPVC NIPPLE TOE SCH80

**MSRP:** 52.76

**Part Code:** 121

**Weight(lbs):** 0.825

**Weight(kg):** 0.374

**Weight(gm):** 374

**Size:** 1" x 22"

**Color:** GRAY

**Material:** CPVC

**Nipple Type** TOE (Plain x Mipt)



**L = 22**

## Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.
- L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.
- M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.
- N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.
- W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

