

**Part No:** 2025-012C

**All**

**INTL-1**

**Desc:** 1-1/4 CPVC GATE VALVE BSP THD EPDM

**MSRP:** 275.07

**Part Code:** 209

**Weight(lbs):** 1.755

**Weight(kg):** 0.796

**Weight(gm):** 796

**Size:** 1-1/4

**Color:**

**Material:**

**Connection** BSP Threaded EPDM

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

