

Part No: 21101J101-015

All

AV-1

Desc: 1-1/2 TRUE UNION 2000 IND BALL VALVE PVC SOC/THD EPDM WITH AIR TO SPRING
80PSI ACTUATOR BASIC MANUAL OVERRIDE

MSRP: 1264.82

Part Code: 530

Weight(lbs): 4.96

Weight(kg): 2.25

Weight(gm): 2250

Size: 1-1/2

Color:

Material:

Connection EPDM Socket

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

