

Part No: 23101H101-012

All

AV-1

Desc: 1-1/4 TRUE UNION 2000 IND BALL VALVE PVC SR THD EPDM WITH DOUBLE ACTING 80PSI AIR TO AIR ACTUATOR BASIC MANUAL OVERRIDE

MSRP: 1206.43

Part Code: 530

Weight(lbs): 4.361

Weight(kg): 1.978

Weight(gm): 1978

Size: 1-1/4

Color:

Material:

Connection EPDM SR Thead

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

