

Part No: 23101H101-060

All

AV-1

Desc: 6 PVC TRUE UNION 2000 IND BALL VALVE SR/FIPT, EPDM W/ 80PSI AIR OPEN - AIR CLOSE PNEUMATIC ACTUATOR, BASIC MANUAL OVERRIDE W/ POSITION INDICATOR

MSRP: 2556.69

Part Code: 530

Weight(lbs): 52.278

Weight(kg): 23.713

Weight(gm): 23713

Size: 6

Color:

Material:

Connection EPDM SR Thead

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

