

Part No: 23102J101-040

All

AV-1

Desc: 4 TRUE UNION 2000 IND BALL VALVE CPVC SR THD EPDM WITH AIR TO SPRING 80PSI ACTUATOR BASIC MANUAL OVERRIDE

MSRP: 2873.98

Part Code: 532

Weight(lbs): 26.623

Weight(kg): 12.076

Weight(gm): 12076

Size: 3

Color:

Material:

Connection EPDM SR Thread

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

