

**Part No:** 23201A112-007

**All**

**AV-1**

**Desc:** 3/4 PVC TRUE UNION 2000 IND BALL VALVE SRFPT FKM W/115VAC REVERSABLE  
ELECTRIC ACTUATOR, 75% DUTY CYCLE, NEMA 4 ENCLOSURE, BASIC MANUAL  
OVERRIDE W/ POSITION INDICATOR

**MSRP:** 1108.46

**Part Code:** 500

**Weight(lbs):** 4.361

**Weight(kg):** 1.978

**Weight(gm):** 1978

**Size:**

**Color:**

**Material:**

**Connection** FKM SR Thread

Under

Development

=

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

