

Part No: 24102J101-012

All

AV-1

Desc: 1-1/4 TRUE UNION 2000 IND BALL VALVE CPVC FLG EPDM WITH AIR TO SPRING 80PSI
ACTUATOR BASIC MANUAL OVERRIDE

MSRP: 1461.02

Part Code: 532

Weight(lbs): 5.044

Weight(kg): 2.288

Weight(gm): 2288

Size:

Color:

Material:

Connection EPDM Flanged

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

