

Part No: 24102J101-040

All

AV-1

Desc: 4 CPVC TRUE UNION 2000 INDUSTRIAL BALL VALVE, FLANGED, EPDM W/ 80PSI AIR OPEN - SPRING CLOSE PNEUMATIC ACTUATOR, BASIC MANUAL OVERRIDE W/ POSITION INDICATOR

MSRP: 3937.1

Part Code: 532

Weight(lbs): 33.021

Weight(kg): 14.978

Weight(gm): 14978

Size: 4

Color:

Material:

Connection EPDM Flanged

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

