

Part No: 24201A112-012

All

AV-1

Desc: 1 1/4 PVC TRUE UNION 2000 IND BALL VALVE FLNG FKM W/ 115VAC REVERSABLE ELECTRIC ACTUATOR, 75% DUTY CYCLE, NEMA 4 ENCLOSURE, BASIC MANUAL OVERRIDE W/ POSITION INDICATOR

MSRP: 1640.88

Part Code: 500

Weight(lbs): 6.169

Weight(kg): 2.798

Weight(gm): 2798

Size:

Color:

Material:

Connection FKM Flanged

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

