

**Part No:** 24201H101-015

**All**

**AV-1**

**Desc:** 1-1/2 TRUE UNION 2000 IND BALL VALVE PVC FLG FKM WITH DOUBLE ACTING 80PSI AIR TO AIR ACTUATOR BASIC MANUAL OVERRIDE

**MSRP:** 1325.33

**Part Code:** 530

**Weight(lbs):** 6.193

**Weight(kg):** 2.809

**Weight(gm):** 2809

**Size:**

**Color:**

**Material:**

**Connection** FKM Flanged

Under

Development

=

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

