

Part No: 24202J101-005

All

AV-1

Desc: 1/2 TRUE UNION 2000 IND BALL VALVE CPVC FLG FKM WITH AIR TO SPRING 80PSI ACTUATOR BASIC MANUAL OVERRIDE

MSRP: 1259.96

Part Code: 532

Weight(lbs): 3.338

Weight(kg): 1.514

Weight(gm): 1514

Size: 1/2

Color:

Material:

Connection FKM Flanged

# Under

# Development

### Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

### Typical Molded Dimension References

