

Part No: 2421-015W

Valves

Single Entry Ball Valve

Desc: 1-1/2 PVC SE BALL VALVE THD EPDM

MSRP: 98.79

Part Code: 240

Weight(lbs): 1.074

Weight(kg): 0.487

Weight(gm): 487

Size: 1-1/2"

Color: WHITE

Material: PVC



Type Single Entry
Connection Fipt
O-Ring EPDM
Pressure Rating 235 psi @ 73° F
Color White

A = 3- 9/16

B = 2- 3/4

C = 4- 5/8

D = 3- 1/16

E = 3- 7/8

Cv = 412

Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

