

Part No: 2432-010W

Valves

Single Entry Ball Valve

Desc: 1 PVC SE BALL VALVE SOC FKM

MSRP: 58.3

Part Code: 240

Weight(lbs): 0.5

Weight(kg): 0.227

Weight(gm): 227

Size: 1"

Color: WHITE

Material: PVC



Type Single Entry
Connection Socket
O-Ring FKM
Pressure Rating 235 psi @ 73° F
Color White

A = 2- 5/8

B = 1- 5/8

C = 3- 7/8

Cv = 146
Values

D = 2- 5/16

E = 3-15/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

