

Part No: 2432-030G

Valves

Single Entry Ball Valve

Desc: 3 PVC SE BALL VALVE SOC FKM

MSRP: 524.51

Part Code: 240

Weight(lbs): 5.187

Weight(kg): 2.353

Weight(gm): 2353

Size: 3"

Color: GRAY

Material: PVC



Type Single Entry
Connection Socket
O-Ring FKM
Pressure Rating 150 psi @ 73° F
Color Gray

A = 6- 3/16

B = 4- 3/8

C = 8- 1/8

Cv = 1660
Values

D = 5- 1/2

E = 7- 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

