

Part No: 2723-007C

Valves

Diaphragm Valve

Desc: 3/4 CPVC DIAPHRAGM VALVE FLANGED EPDM

MSRP: 555.42

Part Code: 272

Weight(lbs): 1.373


Weight(kg): 0.623

Weight(gm): 623

Size: 3/4"

Color: GRAY

Material: CPVC



Connection Flanged
Diaphragm Material EPDM

D = 3- 3/4

E = 3- 1/4

F = 3- 7/8

G = 2- 5/8

No of Bolts = 4

Bolt Circle Dia. = 2- 3/4

Bolt Size = 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

