

**Part No:** 2731-012PSR

**Valves**

**Diaphragm Valve**

**Desc:** 1-1/4 GFPP DIAPHRAGM VALVE SR/THD FKM

**MSRP:** 589.32

**Part Code:** 280

**Weight(lbs):** 2.998

**Weight(kg):** 1.36

**Weight(gm):** 1360

**Size:** 1-1/4"

**Color:** BEIGE

**Material:** Polypropylene



**Connection** SR Fipt

**O-Ring** FKM

**Diaphragm** FKM

**Material**

**A** = 3- 5/16

**B** = 5- 1/2

**C** = 8- 1/4

**D** = 5- 5/8

**E** = 3- 7/8

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

