

Part No: 2731T-005SR

Valves

Diaphragm Valve

Desc: 1/2 PVC DPHRAGM VLV PTFE/EPDM SR/THD FKM

MSRP: 410.4

Part Code: 270

Weight(lbs): 0.864


Weight(kg): 0.392

Weight(gm): 392

Size: 1/2"

Color: GRAY

Material: PVC



Connection SR Fipt

O-Ring FKM

Diaphragm Material PTFE/EPDM

A = 1-15/16

B = 3- 7/8

C = 5- 3/16

D = 3-11/32

E = 2- 7/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

