

Part No: 2731VT-015CSR

Valves

Diaphragm Valve

Desc: 1-1/2 CPVC DPHRM VLV PTFE/FKM SR/THD FKM

MSRP: 1270.32

Part Code: 272

Weight(lbs): 3.829

Weight(kg): 1.737

Weight(gm): 1737

Size: 1-1/2"

Color: GRAY

Material: CPVC



Connection SR Fipt

O-Ring FKM

Diaphragm PTFE/FKM
Material

A = 3-17/32

B = 6- 5/16

C = 8- 7/16

D = 5- 5/8

E = 4- 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

