

Part No: 2731VT-020CSR

Valves

Diaphragm Valve

Desc: 2 CPVC DPHRGM VALVE PTFE/FKM SR/THD FKM

MSRP: 1497.86

Part Code: 272

Weight(lbs): 6.021

Weight(kg): 2.731

Weight(gm): 2731

Size: 2"

Color: GRAY

Material: CPVC



Connection SR Fipt

O-Ring FKM

Diaphragm Material PTFE/FKM

A = 4- 7/32

B = 7- 1/2

C = 9- 1/2

D = 7

E = 6- 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

