

Part No: 2734-020C

All

INTL-1

Desc: 63MM CPVC DIAPHRAGM VALVE FKM DIN SOC

MSRP: 1089.62

Part Code: 276

Weight(lbs): 5.867

Weight(kg): 2.661

Weight(gm): 2661

Size: 63NW50

Color:

Material:

Connection DIN SOC

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

