

Part No: 2793T-030P

Valves

Diaphragm Valve

Desc: 3 GFPP DIAPHRAGM VALVE FLANGED PTFE/EPDM

MSRP: 2486.98

Part Code: 281

Weight(lbs): 15

Weight(kg): 6.804

Weight(gm): 6804

Size: 3

Color: BEIGE

Material: Polypropylene



Connection Flanged
Diaphragm Material PTFE/EPDM

D = 10-3/4

E = 11- 1/8

F = 7-7/16

G = 5- 5/8

No of Bolts = 4

Bolt = 6
Circle Dia.

Bolt Size = 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

