

Part No: 2793T-040

Valves

Diaphragm Valve

Desc: 4 PVC DIAPHRAGM VALVE FLANGED PTFE/EPDM

MSRP: 3068.59

Part Code: 271

Weight(lbs): 26.504

Weight(kg): 12.022

Weight(gm): 12022

Size: 4"

Color: GRAY

Material: PVC



Connection Flanged
Diaphragm Material PTFE/EPDM

D = 12- 3/4

E = 13- 3/16

F = 9

G = 6-23/32

No of Bolts = 8

Bolt Circle Dia. = 7- 1/2

Bolt Size = 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

