

Part No: 280-101823

Fabricated Low Head PIP

Saddles

Desc: 15X10 PVC SADDLE SOC LOW HEAD PIP

MSRP: 76.31

Part Code: 300

Weight(lbs): 2.072

Weight(kg): 0.94

Weight(gm): 940


Size: 15 X 10

Color: WHITE

Material: PVC

Type Saddle-Reducer

Connection Socket



H = 9-9/16

L = 16-1/4

M = 10-7/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

