





**Turf & Irrigation
PVC 80, 100 & 125 PSI PIP Fabricated Fittings**

Size	80 PSI	100 PSI	125 PSI
	Disc Code: 310 Part Number Price Each	Disc Code: 320 Part Number Price Each	Disc Code: 330 Part Number Price Each

Reducer Coupling (Gasket x Spigot) (continued)


	21X15	2929-85523 1300.69	---	---
	21X18	2929-85823 1022.29	300-101344 1296.31	3329-85823P 1382.38
	24X6	2929-90623 3142.17	3029-90623 3350.97	3329-90623P 3652.01
	24X8	2929-90823 2981.18	3029-90823 3126.30	3329-90823P 3297.21
	24X10	2929-91023 2837.82	3029-91023 2990.39	3329-91023P 3211.72
	24X12	2929-91223 2483.91	3029-91223 2631.28	3329-91223P 2811.24
	24X15	2929-91523 1807.12	3029-91523 1951.70	3329-91523P 2554.67
	24X18	2929-91823 1714.72	3029-91823 1925.30	3329-91823P 2431.73
	24X21	2929-92123 1525.50	3029-92123 1892.93	3329-92123P 2318.56
	27X6	2929-93623 4085.49	3029-93623 4361.53	3329-93623P 4709.76
	27X8	2929-93823 3799.89	3029-93823 4124.30	3329-93823P 4402.87
	27X10	2929-94023 3562.79	3029-94023 3806.98	3329-94023P 4056.84
	27X12	2929-94223 3345.15	3029-94223 3547.55	3329-94223P 3830.49
	27X15	2929-94523 2635.64	3029-94523 2816.28	3329-94523P 3345.15
	27X18	2929-94823 2465.88	3029-94823 2644.34	3329-94823P 3235.63
	27X21	2929-95123 2180.76	3029-95123 2454.99	3329-95123P 3190.62
	27X24	2929-95423 2135.56	3029-95423 2685.26	3329-95423P 3157.11

Reducer Coupling (Spigot x Gasket)


	6X4	2929-53232 79.04	300-101383 81.94	3329-53232P 105.44
	8X4	2929-58232 180.96	3029-58232 193.94	3329-58232P 225.63
	8X6	2929-58532 95.90	300-101385 114.19	3329-58532P 121.86
	10X4	2929-62432 264.49	3029-62432 288.30	3329-62432P 316.82
	10X6	2929-62632 205.56	3029-62632 225.85	3329-62632P 257.79
	10X8	2929-62832 150.70	300-101388 170.37	3329-62832P 217.60
	12X4	2929-66432 356.84	3029-66432 372.18	3329-66432P 521.82
	12X6	2929-66632 327.18	3029-66632 348.62	3329-66632P 502.65
	12X8	2929-66832 228.00	3029-66832 263.40	3329-66832P 439.90
	12X10	2929-67032 218.02	300-101392 241.30	3329-67032P 307.76
	15X4	2929-72432 769.37	3029-72432 823.24	3329-72432P 1037.98
	15X6	2929-72632 727.36	3029-72632 778.30	3329-72632P 846.87
	15X8	2929-72832 682.62	3029-72832 737.23	3329-72832P 782.70
	15X10	2929-73032 470.84	3029-73032 589.56	3329-73032P 683.68
	15X12	2929-73232 320.15	300-101397 373.00	3329-73232P 529.15
	18X4	2929-78432 1592.76	3029-78432 1681.23	3329-78432P 1780.63
	18X6	2929-78632 1559.28	3029-78632 1645.04	3329-78632P 1743.57
	18X8	2929-78832 1437.30	3029-78832 1523.65	3329-78832P 1630.33
	18X10	2929-79032 924.78	3029-79032 997.37	3329-79032P 1127.10

Size	80 PSI	100 PSI	125 PSI
	Disc Code: 310 Part Number Price Each	Disc Code: 320 Part Number Price Each	Disc Code: 330 Part Number Price Each

Reducer Coupling (Spigot x Gasket) (continued)

	18X12	2929-79232 906.81	3029-79232 936.85	3329-79232P 1062.20
	18X15	2929-79532 627.70	300-101403 721.49	3329-79532P 810.12
	21X6	2929-84632 1821.78	3029-84632 1931.15	3329-84632P 2056.61
	21X8	2929-84832 1581.26	3029-84832 1596.47	3329-84832P 1684.56
	21X10	2929-85032 1385.81	3029-85032 1487.30	3329-85032P 1537.71
	21X12	2929-85232 1309.85	3029-85232 1362.11	3329-85232P 1442.73
	21X15	2929-85532 1248.66	3029-85532 1323.31	3329-85532P 1405.88
	21X18	2929-85832 964.50	300-101417 1087.48	3329-85832P 1262.36
	24X6	2929-90632 3016.48	3029-90632 3216.93	3329-90632P 3506.02
	24X8	2929-90832 2861.93	3029-90832 3001.24	3329-90832P 3165.32
	24X10	2929-91032 2724.31	3029-91032 2870.78	3329-91032P 3083.38
	24X12	2929-91232 2384.79	3029-91232 2526.03	3329-91232P 2698.78
	24X15	2929-91532 1735.09	3029-91532 1875.17	3329-91532P 2452.49
	24X18	2929-91832 1646.13	3029-91832 1848.28	3329-91832P 2333.72
	24X21	2929-92132 1501.16	3029-92132 1807.84	3329-92132P 2010.61
	27X6	2929-93632 3922.06	3029-93632 4187.23	3329-93632P 4521.37
	27X8	2929-93832 3647.90	3029-93832 3959.07	3329-93832P 4222.95
	27X10	2929-94032 3420.19	3029-94032 3654.71	3329-94032P 3894.56
	27X12	2929-94232 3211.34	3029-94232 3405.66	3329-94232P 3677.28
	27X15	2929-94532 2530.38	3029-94532 2703.62	3329-94532P 3210.50
27X18	2929-94832 2367.24	3029-94832 2538.57	3329-94832P 3106.20	
27X21	2929-95132 2093.52	3029-95132 2356.79	3329-95132P 2878.98	
27X24	2929-95432 2097.91	3029-95432 2512.72	3329-95432P 3030.15	

Reducer Coupling (Gasketed)

	6X4	2929-5322 96.12	300-101456 114.19	3329-5322P 145.18
	8X4	2929-5822 215.33	3029-5822 230.79	3329-5822P 268.49
	8X6	2929-5852 121.57	300-101458 150.33	3329-5852P 186.86
	10X4	2929-6242 314.73	3029-6242 343.07	3329-6242P 375.73
	10X6	2929-6262 245.01	3029-6262 268.77	3329-6262P 306.78
	10X8	2929-6282 213.30	300-101461 241.30	3329-6282P 301.60
	12X4	2929-6642 424.64	3029-6642 443.09	3329-6642P 620.97
	12X6	2929-6662 389.35	3029-6662 414.86	3329-6662P 598.16
	12X8	2929-6682 317.32	3029-6682 370.38	3329-6682P 523.48
	12X10	2929-6702 286.54	300-101465 331.03	3329-6702P 417.00
	15X4	2929-7242 916.69	3029-7242 979.78	3329-7242P 1235.26
	15X6	2929-7262 865.56	3029-7262 926.17	3329-7262P 1008.72
	15X8	2929-7282 812.31	3029-7282 877.31	3329-7282P 931.41