

**Turf & Irrigation
PVC 80, 100 & 125 PSI PIP Fabricated Fittings**



Size	80 PSI	100 PSI	125 PSI
	Disc Code: 310 Part Number Price Each	Disc Code: 320 Part Number Price Each	Disc Code: 330 Part Number Price Each

22-1/2° Elbow (Gasket x Spigot)

	6	290-100426 93.23	300-100426 114.19	3316-06023P 132.99
	8	290-100427 151.50	300-100427 169.00	3316-08023P 197.91
	10	290-100428 227.28	300-100428 250.56	3316-10023P 290.39
	12	290-100429 308.84	300-100429 361.32	3316-12023P 419.88
	15	290-100430 544.33	300-100430 596.76	3316-15023P 706.35
	18	290-100431 862.52	300-100431 988.41	3316-18023P 1174.93
	21	290-100433 1273.97	300-100433 1370.76	3316-21023P 1782.19
	24	2916-24023 2108.47	3016-24023 2386.01	3316-24023P 2995.09
	27	2916-27023 2727.97	3016-27023 3085.71	3316-27023P 3729.26

22-1/2° Elbow (Gasketed)

	6	290-100450 93.23	300-100450 114.19	3316-0602P 132.99
	8	290-100451 151.50	300-100451 169.00	3316-0802P 197.91
	10	290-100452 227.28	300-100452 250.56	3316-1002P 290.39
	12	290-100453 308.84	300-100453 361.32	3316-1202P 419.88
	15	290-100454 544.33	300-100454 596.76	3316-1502P 706.35
	18	290-100455 862.52	300-100455 988.41	3316-1802P 1174.93
	21	290-100457 1273.97	300-100457 1370.76	3316-2102P 1782.19
	24	2916-2402 2108.47	3016-2402 2386.01	3316-2402P 2995.09
	27	2916-2702 2727.97	3016-2702 3085.71	3316-2702P 3729.26

30° Elbow (Socket)

	6	290-100474 47.76	300-100474 50.12	3315-060P 64.11
	8	290-100475 72.29	300-100475 87.40	3315-080P 108.22
	10	290-100476 111.84	300-100476 131.69	3315-100P 163.80
	12	290-100477 160.81	300-100477 195.81	3315-120P 217.18
	15	290-100478 254.07	300-100478 304.21	3315-150P 376.46
	18	290-100479 414.94	300-100479 507.02	3315-180P 635.22
	21	290-100481 671.38	300-100481 818.27	3315-210P 1030.37
	24	290-100482 1915.10	300-100482 2226.30	3315-240P 2337.04
	27	2915-270 2110.82	3015-270 2374.79	3315-270P 2616.14

30° Elbow (Gasket x Spigot)

	6	290-100546 116.52	300-100546 134.04	3315-06023P 160.05
	8	290-100547 174.82	300-100547 189.97	3315-08023P 225.86
	10	290-100548 245.90	300-100548 272.73	3315-10023P 319.40
	12	290-100549 331.03	300-100549 388.14	3315-12023P 456.13
	15	290-100550 673.71	300-100550 785.61	3315-15023P 877.67
	18	290-100551 946.44	300-100551 1113.11	3315-18023P 1391.68
	21	290-100553 1410.36	300-100553 1204.94	3315-21023P 1981.52
	24	2915-24023 2262.72	3015-24023 3102.89	3315-24023P 3214.02

Size	80 PSI	100 PSI	125 PSI
	Disc Code: 310 Part Number Price Each	Disc Code: 320 Part Number Price Each	Disc Code: 330 Part Number Price Each

30° Elbow (Gasket x Spigot) (continued)

	27	2915-27023 3057.07	3015-27023 3567.53	3315-27023P 4177.83
--	----	-----------------------	-----------------------	------------------------

30° Elbow (Gasketed)

	6	290-100570 116.52	300-100570 134.04	3315-0602P 160.05
	8	290-100571 174.82	300-100571 189.97	3315-0802P 225.86
	10	290-100572 245.90	300-100572 272.73	3315-1002P 319.40
	12	290-100573 331.03	300-100573 388.14	3315-1202P 456.13
	15	290-100574 673.71	300-100574 785.61	3315-1502P 877.67
	18	290-100575 946.44	300-100575 1113.11	3315-1802P 1391.68
	21	290-100577 1410.36	300-100577 1204.94	3315-2102P 1981.52
	24	2915-2402 2262.97	3015-2402 3102.89	3315-2402P 3214.02
	27	2915-2702 3057.07	3015-2702 3567.53	3315-2702P 4177.83

45° Elbow (Socket)

	6	290-100592 47.76	300-100592 50.12	3317-060P 64.13
	8	290-100593 72.29	300-100593 87.40	3317-080P 108.22
	10	290-100594 111.84	300-100594 131.69	3317-100P 163.80
	12	290-100595 160.81	300-100595 195.81	3317-120P 217.18
	15	290-100596 254.07	300-100596 304.21	3317-150P 376.46
	18	290-100597 414.94	300-100597 507.02	3317-180P 635.22
	21	290-100599 671.38	300-100599 818.27	3317-210P 1030.37
	24	290-100600 1915.10	300-100600 2226.30	3317-240P 2337.04
	27	2917-270 2110.82	3017-270 2374.79	3317-270P 2616.14

45° Elbow (Gasket x Spigot)

	6	290-100658 116.52	300-100658 134.04	3317-06023P 160.05
	8	290-100659 174.82	300-100659 189.97	3317-08023P 225.86
	10	290-100660 245.90	300-100660 272.73	3317-10023P 319.40
	12	290-100661 331.03	300-100661 388.14	3317-12023P 456.13
	15	290-100662 673.71	300-100662 785.61	3317-15023P 877.67
	18	290-100663 946.44	300-100663 1113.11	3317-18023P 1391.68
	21	290-100665 1410.36	300-100665 1204.94	3317-21023P 1981.52
	24	2917-24023 2262.97	3017-24023 3102.89	3317-24023P 3214.02
	27	2917-27023 3057.07	3017-27023 3567.53	3317-27023P 4177.83