

**Part No:** 330-100117

**All**

**CLS-1**

**Desc:** 12 PVC 11-1/4 ELL SOC CL125

**MSRP:** 347.8

**Part Code:** 360

**Weight(lbs):** 14.103

**Weight(kg):** 6.397

**Weight(gm):** 6397

**Size:** 12

**Color:**

**Material:**

**Connection** Soc x Soc Class 125

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

