

Part No: 330-100332

All

CLS-1

Desc: 10 PVC 15 ELL GASKET CL125

MSRP: 537.42

Part Code: 360

Weight(lbs): 20.342

Weight(kg): 9.227

Weight(gm): 9227

Size: 10

Color:

Material:

Connection Gasket x Gasket Class 125

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

