

**Part No:** 3315-0602P

**All**

**PIP-1**

**Desc:** 6 PVC 30 ELL GASKET 125PIP

**MSRP:** 268.79

**Part Code:** 330

**Weight(lbs):** 5.313

**Weight(kg):** 2.41

**Weight(gm):** 2410

**Size:** 6

**Color:**

**Material:**

**Connection** Gasketed 125 PSI

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

