

Part No: 3316-1002P

All

PIP-1

Desc: 10 PVC 22-1/2 ELL GASKET 125PIP

MSRP: 487.69

Part Code: 330

Weight(lbs): 14.639

Weight(kg): 6.64

Weight(gm): 6640

Size: 10

Color:

Material:

Connection Gasketed 125 PSI

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

