

**Part No:** 340-100331

**All**

**CLS-1**

**Desc:** 8 PVC 15 ELL GASKET CL160

**MSRP:** 437.24

**Part Code:** 370

**Weight(lbs):** 12.346

**Weight(kg):** 5.6

**Weight(gm):** 5600

**Size:** 8

**Color:**

**Material:**

**Connection** Gasket x Gasket Class 160

## Under

## Development

### Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

### Typical Molded Dimension References

