

Part No: 340-102427

All

CLS-1

Desc: 4X2 PVC RED TEE GASKETXGASKETXFPT

MSRP: 333.89

Part Code: 370

Weight(lbs): 5.159

Weight(kg): 2.34

Weight(gm): 2340

Size: 4 X 2

Color:

Material:

Connection Gasket x Gasket x Fipt Class 160

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

