

**Part No:** 3622R-040C

**All**

**BV-1**

**Desc:** 4 CPVC TU2K STANDARD BV RTF/SOC EPDM

**MSRP:** 1410.19

**Part Code:** 611

**Weight(lbs):** 15.263

**Weight(kg):** 6.923

**Weight(gm):** 6923

**Size:** 4

**Color:**

**Material:**

**Connection** CPVC Socket Ends

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

