

Part No: 3627-007

Valves

True Union Ball Valve

Desc: 3/4 PVC TU2K STANDARD BV SPIGOT EPDM

MSRP: 79

Part Code: 608

Weight(lbs): 0.578


Weight(kg): 0.262

Weight(gm): 262

Size: 3/4"

Color: GRAY

Material: PVC



D = 2

E = 3

Cv = 63
Values

A = 2- 1/4

B = 3- 1/4

C = 5- 1/4

Type TU 2000 - Standard
O-Ring EPDM
Connection Spigot
Pressure Rating 235 psi @ 73° F

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006