

Part No: 3632R-030C

All

BV-1

Desc: 3 CPVC TU2K STANDARD BV RTF-SOC FKM

MSRP: 864.78

Part Code: 611

Weight(lbs): 8.931

Weight(kg): 4.051

Weight(gm): 4051

Size:

Color:

Material:

Connection CPVC Socket Ends

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

