

Part No: 3634-010C

All

INTL-1

Desc: 32NW25 CPVC TU2000 STD BV FKM PLN

MSRP: 146.9

Part Code: 239

Weight(lbs): 0.807

Weight(kg): 0.366

Weight(gm): 366

Size: 32MM

Color:

Material:

Connection DIN SOC

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

