

Part No: 3701-120

Fabricated DWV

Tees

Desc: 12 PVC TEE SOC SCH40

MSRP: 782.93

Part Code: 390

Weight(lbs): 38.131

Weight(kg): 17.296

Weight(gm): 17296

Size: 12


Color: WHITE

Material: PVC

Type Standard Vent Tee

Schedule SCH 40 DWV

Connection Socket x Socket x Socket



G = 11-1/4

G1 = 10-3/16

H = 17-1/2

H1 = 16-7/16

L = 35

M = 13-9/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

