

Part No: 3701-624

Fabricated DWV

Tees

Desc: 10X4 PVC RED TEE SOC SCH40

MSRP: 320.91

Part Code: 390

Weight(lbs): 14.253


Weight(kg): 6.465

Weight(gm): 6465

Size: 10 X 4

Color: WHITE

Material: PVC



Type Reducing Vent Tee
Schedule SCH 40 DWV
Connection Socket x Socket x Socket

G = 5-3/8

G1 = 8-5/16

H = 10-5/8

H1 = 10-9/16

L = 21-1/4

M = 11-1/2

M1 = 5

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

