

Part No: 3720-818

Fabricated DWV

Crosses

Desc: 20X8 PVC RED CROSS SOC SCH40

MSRP: 3281.33

Part Code: 390

Weight(lbs): 82.825


Weight(kg): 37.569

Weight(gm): 37569

Size: 20X8

Color: WHITE

Material: PVC



Type Reduction
Schedule SCH 40 DWV
Connection Soc x Soc x Soc x Soc

L1 = 34

M = 21-3/16

M1 = 9-1/4

G = 8-1/4

G1 = 12-3/4

H = 18-1/4

H1 = 17

L = 36-1/2

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

