

Part No: 3776-200

Fabricated DWV

Double Wye

Desc: 20 PVC DBL-WYE SOC SCH40 N.P.R.

MSRP: 4841.09

Part Code: 390

Weight(lbs): 232.526

Weight(kg): 105.472

Weight(gm): 105472

Size: 20"


Color: WHITE

Material: PVC

Schedule SCH 40 DWV

Type Standard

Connection Socket x Socket x Socket x Socket



G1 = 11-7/16

G2 = 30-5/16

G3 = 30-5/16

H1 = 21-7/16

H2 = 40-5/16

H3 = 40-5/16

L = 61-3/4

M = 21-3/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

