

Part No: 3776-822

Fabricated DWV

Double Wye

Desc: 20X12 PVC RD DBL-WYE SOC S40 NPR.

MSRP: 3592.89

Part Code: 390

Weight(lbs): 1309.546

Weight(kg): 594

Weight(gm): 594000

Size: 20"X20"X12"X12"


Color: WHITE

Material: PVC

Schedule SCH 40 DWV

Type Reducing

Connection Socket x Socket x Socket x Socket



G1 = 4-3/8

G2 = 24-3/8

G3 = 24-15/16

H1 = 14-3/8

H2 = 34-3/8

H3 = 31-3/16

L = 48-3/4

M = 21-3/16

M1 = 13-9/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ inch & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

