

Part No: 3777-532

Fabricated DWV

Combo Wye & 1/8 Bend

Desc: 6X4 PVC RD CMB Y&1/8BND SOC SCH40

MSRP: 245.7

Part Code: 390

Weight(lbs): 8.113

Weight(kg): 3.68

Weight(gm): 3680


Size: 6"X6"X4"

Color: WHITE

Material: PVC

Schedule SCH 40 DWV- Reducing

Connection Socket x Socket x Socket



G1 = 1/16

G2 = 11-11/16

G3 = 11-5/16

H = 13-1/16

L = 18-1/4

M = 7-3/16

M1 = 5-1/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

